burster

Precision and High-Precision Resistors

Series 1140

1150


1160


Model 1178


Code: 1100 EN

Delivery: ex stock (standard values)

Warranty: 36 months







- $TC \le 2 ppm/K \text{ or } \le 10 ppm/K$
- Class ± 0.01 % or ± 0.02 % or ± 0.05 % or ± 0.1 %
- Production range from 1 m Ω ... 100 k Ω
- Resistance material ZERANIN® or MANGANIN® or ISA-Ohm
- Standard values available from stock
- Custom resistance values available on request

Application

Precision and high-precision resistors are used wherever the highest standards of temperature stability, error tolerance and durability are required.

Model 1142 and 1152 high-precision resistors, with tolerances at values of \leq 0.01%, are equivalent to standard resistors and can be used as substitutes in many cases. Models 1152 and 1156 are available for higher loads up to 1 W.

If requirements for the temperature coefficients and longterm stability are less strict, MANGANIN® or ISA-Ohm resistors can be used.

The low-ohm model 1178 precision resistors feature separate current and voltage paths to compensate errors caused feed by line resistances. The separate current and voltage paths enable these resistors to be used as a high-precision shunt in many measurement arrangements.

Description

The resistors are supplied with two connections on the front end (suitable for mounting on circuit boards).

The high-precision resistors comprise low-capacitance, lowinductance wire coils made of ZERANIN®, MANGANIN® or ISA-Ohm, which are encapsulated in small plastic cylinder housings.

Prior to trimming, the resistance bodies are exposed to a meticulous artificial aging procedure. This special process and trimming to approximately half of the nominal tolerance guarantee long-term stability of < 0.01% (ZERANIN®) or < 0.02% (MANGANIN® or ISA-Ohm) over the course of years.

The temperature coefficient with the MANGANIN® material attains values of ≤ 10 ppm/K. By selecting materials, values of ≤ 2 ppm/K are achieved with ZERANIN®.

Within the specified production range, any desired resistance value can be supplied.

V
burster

1142	1146	1152	1156	1164	1166	1178
						*
	*		*		*	*
	*		*		*	
	*		*		*	
*	*	*		*		
	*	*		*		
100 Ω up to 40 k Ω	5Ω up to 100 kΩ	1156: 5 Ω 1152:100 Ω	Ω up to 100 Ω 1166: Ω up Ω 0 up to 100 k Ω 1164:100 Ω up		up to 100 Ω up to 100 $k\Omega$	on request in the range of 1 m Ω up to 5 Ω
± 0.01 %	± 0.05 %	± 0.01 %	± 0.05 %	± 0.02 %	± 0.05 %	± 0.1 %
ZERANIN® selected	MANGANIN® or ISA-Ohm					MANGANIN® or ISO-Ohm
< ± 2 ppm/K	< ± 10 ppm/K	< ± 2 ppm/K		< ± 10 ppm/K		< ± 10 ppm/K
0.7 W	0.7 W	1 W		1 W		1 W (max. 6 A)
0.01 % over years	0.02 % over years	0.01 % over years		0.02 % over years		0.02 % of years
90 K/W	90 K/W	60 K/W		60 K/W		60 K/W
Ø 10.5 Models					0 12 Model 1178 29 ±1 Ca. 30	
	* 100 Ω up to 40 kΩ ± 0.01 % ZERANIN® selected < ± 2 ppm/K 0.7 W 0.01 % over years 90 K/W Models 1142 1144 1146	* * * * 100 Ω up to 40 kΩ \$\frac{\pi}{2}\$ \$\frac{\pi}{2}\$ up to 100 kΩ \$\frac{\pi}{2}\$ 0 ISA-Ohm \$\frac{\pi}{2}\$ 0.7 W \$\frac{\pi}{2}\$ 0.7 W \$\frac{\pi}{2}\$ 0.7 W \$\frac{\pi}{2}\$ 0.7 W \$\frac{\pi}{2}\$ 0.8 \pi \frac{\pi}{2}\$ 0.8 \pi \p	* * * * * * * * * 100 Ω up to 40 kΩ 5 Ω up to 100 kΩ 1156: 5 Ω 1152:100 Ω ± 0.01 % 2ERANIN® selected or ISA-Ohm selected < ± 2 ppm/K 0.7 W 0.7 W 1 0.01 % over years 90 K/W 90 K/W 00 K/W 00 K/W 00 K/W 00 K/W 01 Models 1142 1144 1146 116 116 116 116 116 116 116 1	* * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * * *	* * * * * * * * * * * * * * * * * * *	* * * * * * * * * * * * * * * * * * *

Operating voltage:

Weight

approx. 3 g max. 500 V

Special values

approx. 8 g

Calibration temperature:

23 °C

for connecting wire of 5 mm range 0 °C ... + 85 °C

approx. 3 g

Temperature operating range: Short-time over load:

approx. 10 % < 1 min.

Specifications:

Balance point:

according DIN 43783 part 1

(former VDE 410)

Extra charge per piece for special values, refer to order no.

Minimum order quantity: 5 pcs of identical version,

smaller quantities are available on

approx. 6 g

1199S

extra charges.

Delivery:

approx. 8 weeks

approx. 8 g

Temperature dependence

ZERANIN®:

 $= R_0 (1 + a^* t + b^* t^2 + g^* t^3)$

 $= 1.22 \cdot 10^{-5}$ α - 2.12 · 10⁻⁷ β $= +9.44 \cdot 10^{-10}$

t = Element temperature in °C Resistance value at 0 °C Resistance value at temperature t

MANGANIN®:

= $R_{20}(1 + a_{20}(t - 20) + b(t - 20)^2)$

0 ... 20 · 10-6 $\alpha_{20} =$

- 0.59 · 10⁻⁶ β Resistance value at 20 °C $R_{20} =$

Order Code

5 pcs 1152 - 100.0 Ω (Standard model) 12 pcs 1146S - 153.8 Ω (Special model)